


Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
PD1647-3	.750 (19.05)	.520 (13.21)	.39 (9.91)	.690 (17.53)	.100 (2.54)	.476 (12.09)	.394 (10.01)	.045 (1.14)	.060 (1.52)	.276 (7.01)	.194 (4.93)	.257 (6.53)	.560 (14.22)

CASE #	P	Q	R	S	T	U	V	WT, GRAM
PD1647-3	.475 (12.07)	.561 (14.25)	.258 (6.55)	.069 (1.75)	.061 (1.55)	.030 (0.76)	.433 (11.00)	2.60

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Heat sink material: Black anodized aluminum alloy.
2. Base material: Printed wiring laminate.
3. Termination finish: Tin copper solder alloy up to 0.07% Nickel. All models, (+) suffix.