

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.00	43.4	43.5
200.0	0.01	38.0	38.1
300.0	0.02	34.5	34.7
400.0	0.02	33.1	33.6
500.0	0.03	32.4	32.8
600.0	0.03	32.8	33.1
700.0	0.03	34.6	34.8
800.0	0.03	37.4	37.8
900.0	0.04	44.2	45.5
1000.0	0.04	50.3	49.5
1100.0	0.04	39.1	39.3
1200.0	0.04	34.9	35.1
1300.0	0.04	32.4	32.7
1400.0	0.04	31.5	31.7
1500.0	0.05	31.5	31.5
1600.0	0.05	32.0	32.4
1700.0	0.05	33.6	33.8
1800.0	0.05	36.1	36.7
1900.0	0.06	39.4	41.1
2000.0	0.06	40.6	42.7
2400.0	0.07	33.3	33.3
3000.0	0.08	38.8	40.8
4000.0	0.09	37.1	39.5
5000.0	0.10	34.1	34.7
6000.0	0.12	32.7	35.3
7000.0	0.14	36.0	37.3
8000.0	0.15	37.6	35.5
9000.0	0.16	38.2	34.0
10000.0	0.15	41.5	35.1
11000.0	0.18	32.8	28.3
12000.0	0.21	31.6	28.2
13000.0	0.23	31.6	29.4
14000.0	0.23	29.5	25.2
15000.0	0.26	27.7	24.3
16000.0	0.27	25.4	23.8
17000.0	0.28	26.6	25.8
18000.0	0.31	28.2	28.0