

Hand-Flex Coaxial Cable, SMA-M/N-M

141-7SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.01	45.1	45.3
200.0	0.02	38.7	39.3
300.0	0.03	37.0	37.5
500.0	0.03	39.0	40.5
600.0	0.03	43.1	46.0
800.0	0.04	44.1	42.7
900.0	0.04	39.4	38.8
1000.0	0.04	37.1	37.1
1200.0	0.04	38.3	40.2
1400.0	0.05	47.9	48.5
1600.0	0.05	39.0	36.3
1800.0	0.06	36.1	35.6
2000.0	0.06	39.9	42.9
2200.0	0.06	52.6	41.3
2400.0	0.06	37.8	35.8
2600.0	0.07	36.2	37.6
2800.0	0.07	41.0	41.4
3000.0	0.07	43.4	36.6
3500.0	0.07	40.8	39.0
4000.0	0.08	41.5	37.5
4500.0	0.08	33.9	32.1
5000.0	0.09	34.4	33.9
5500.0	0.10	39.9	39.7
6000.0	0.10	36.2	34.4
6500.0	0.11	30.1	31.4
7000.0	0.12	28.4	28.4
7500.0	0.12	34.7	34.4
8000.0	0.13	28.0	28.2
8500.0	0.16	23.2	23.4
9000.0	0.15	26.6	25.8
9500.0	0.15	43.4	39.9
10000.0	0.18	23.1	23.2
10500.0	0.20	21.1	20.9
11000.0	0.18	26.3	25.4
11500.0	0.18	30.4	29.8
12000.0	0.22	21.0	21.3
12500.0	0.23	20.5	20.4
13000.0	0.21	25.6	25.4
13500.0	0.20	40.5	48.5
14000.0	0.24	22.7	23.0
14500.0	0.25	21.4	21.4
15000.0	0.23	24.2	24.2
15500.0	0.23	25.5	26.4
16000.0	0.23	26.4	27.1
16500.0	0.25	23.5	22.7
17000.0	0.27	21.2	21.4
17500.0	0.26	25.2	26.5
18000.0	0.26	28.7	28.2