

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.50	0.56	15.26
0.60	0.55	16.52
0.70	0.55	17.47
0.80	0.54	18.19
0.90	0.54	18.76
1.00	0.55	19.20
4.00	0.41	23.25
7.00	0.36	24.59
10.00	0.35	25.10
15.00	0.35	25.38
20.00	0.36	25.41
48.00	0.39	24.28
76.00	0.43	22.55
104.00	0.48	20.89
132.00	0.51	19.41
160.00	0.54	18.10
188.00	0.59	16.96
216.00	0.65	15.97
244.00	0.68	15.08
272.00	0.72	14.30
300.00	0.82	13.59
320.00	0.85	13.13
340.00	0.86	12.71
360.00	0.89	12.32
380.00	0.97	11.96
400.00	1.05	11.62
420.00	1.08	11.31
440.00	1.09	11.02
460.00	1.15	10.75
480.00	1.25	10.51
500.00	1.30	10.28
515.00	1.32	10.12
530.00	1.34	9.97
545.00	1.37	9.81
560.00	1.45	9.69
575.00	1.52	9.56
590.00	1.56	9.44
605.00	1.57	9.34
620.00	1.60	9.25
635.00	1.65	9.16
650.00	1.72	9.09