

Coaxial High Pass Filter

BHP-250+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	72.15	0.03	100.0	2.230
100.0	57.26	0.08	129.0	2.630
130.0	40.71	0.18	130.0	2.590
140.0	35.39	0.20	140.0	2.900
150.0	30.09	0.22	150.0	3.170
160.0	24.78	0.26	160.0	3.630
166.0	21.57	0.29	166.0	4.000
167.0	21.04	0.31	167.0	4.070
170.0	19.43	0.34	170.0	4.320
180.0	14.04	0.53	180.0	5.390
185.0	11.37	0.71	185.0	6.140
186.0	10.84	0.76	186.0	6.310
187.0	10.31	0.82	187.0	6.490
188.0	9.80	0.88	188.0	6.690
189.0	9.28	0.94	189.0	6.890
190.0	8.77	1.02	190.0	7.090
199.0	4.65	2.21	199.0	9.190
200.0	4.26	2.43	200.0	9.410
201.0	3.90	2.67	201.0	9.630
202.0	3.56	2.93	202.0	9.830
203.0	3.24	3.23	203.0	10.020
204.0	2.94	3.56	204.0	10.180
205.0	2.66	3.91	205.0	10.320
206.0	2.41	4.31	206.0	10.430
207.0	2.17	4.73	207.0	10.510
208.0	1.96	5.20	208.0	10.560
209.0	1.77	5.71	209.0	10.580
210.0	1.60	6.27	210.0	10.580
211.0	1.44	6.87	211.0	10.540
212.0	1.30	7.51	212.0	10.470
213.0	1.18	8.21	213.0	10.370
214.0	1.08	8.97	214.0	10.240
215.0	0.99	9.78	215.0	10.090
216.0	0.90	10.65	216.0	9.920
225.0	0.55	23.49	225.0	8.030
250.0	0.42	17.28	250.0	4.820
300.0	0.30	30.05	300.0	2.940
350.0	0.28	28.44	350.0	2.070
400.0	0.23	27.07	400.0	1.590
450.0	0.21	30.82	450.0	1.290
500.0	0.19	33.64	500.0	1.090
550.0	0.19	33.90	550.0	0.940
600.0	0.19	30.85	600.0	0.830
650.0	0.19	29.50	650.0	0.740
700.0	0.19	28.81	700.0	0.670
750.0	0.19	28.39	750.0	0.630
800.0	0.20	28.48	800.0	0.580
850.0	0.20	28.65	850.0	0.550
900.0	0.20	29.04	900.0	0.520
950.0	0.20	29.40	950.0	0.490
1000.0	0.20	29.79	1000.0	0.470
1500.0	0.24	29.34	1500.0	0.370
2000.0	0.29	27.11	2000.0	0.340
2500.0	0.38	21.50	2500.0	0.330
3000.0	0.51	16.22	3000.0	0.320

REV. X1
BHP-250+
070628
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

