

Switch SP4T, 50Ω

GSWA-4-30DR+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS TTL Low @ 0V (dB) IN-OUT, "ON"	ISOLATION TTL High @ 5V (dB) IN-OUT, "OFF"	VSWR (:1)		
			IN	OUT, "ON"	OUT, "OFF"
10.0	0.58	81.27	1.04	1.05	1.09
46.0	0.73	77.05	1.07	1.04	1.08
64.0	0.77	72.78	1.05	1.05	1.08
100.0	0.82	75.11	1.05	1.06	1.07
260.0	0.97	68.08	1.14	1.11	1.07
420.0	1.10	60.51	1.21	1.16	1.08
600.0	1.23	56.91	1.25	1.21	1.06
800.0	1.31	53.59	1.30	1.28	1.08
1000.0	1.44	50.26	1.39	1.32	1.09
1200.0	1.49	48.06	1.43	1.35	1.10
1400.0	1.61	45.78	1.44	1.36	1.12
1600.0	1.70	43.73	1.50	1.39	1.12
1800.0	1.76	41.79	1.57	1.42	1.12
2000.0	1.92	40.34	1.49	1.40	1.15
2200.0	2.05	39.17	1.64	1.48	1.12
2400.0	2.18	38.05	1.69	1.50	1.14
2600.0	2.36	37.08	1.65	1.68	1.13
2800.0	2.57	36.32	1.65	1.75	1.11
3000.0	2.88	35.55	1.84	2.00	1.13