

Ceramic Low Pass Filter

LFCN-575D+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
1.0	0.07	1.01
50.0	0.15	1.03
100.0	0.21	1.03
200.0	0.31	1.02
250.0	0.36	1.00
300.0	0.41	1.01
350.0	0.47	1.03
400.0	0.53	1.04
450.0	0.60	1.05
500.0	0.69	1.05
575.0	0.84	1.08
600.0	0.91	1.11
680.0	1.25	1.30
700.0	1.38	1.37
770.0	2.04	1.66
800.0	2.52	1.83
850.0	4.98	2.97
875.0	8.55	4.95
900.0	14.04	7.79
945.0	26.78	11.71
1000.0	34.06	14.39
1050.0	35.93	16.26
1100.0	39.86	18.01
1200.0	40.35	21.23
1300.0	39.08	24.41
1400.0	40.34	27.54
1500.0	42.79	30.46
1600.0	45.67	33.29
1700.0	48.14	35.94
1800.0	49.58	38.24
1900.0	50.37	40.09
2000.0	51.19	41.85
2500.0	54.82	46.25
3000.0	48.54	47.85
3500.0	42.23	47.41
4000.0	37.25	42.08
4500.0	35.09	34.48
5000.0	20.11	21.33
5500.0	22.12	24.18

