

Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB	USB	LSB	USB	LSB	USB	LSB	USB	
(MHz)	(dB)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(mV)
95.0	5.38	39.29	44.75	52.53	52.54	48.67	54.98	76.21	73.88	0.21
95.8	5.39	39.55	44.33	52.71	52.13	48.79	55.31	76.43	73.83	0.20
96.5	5.39	39.78	44.03	52.17	52.17	48.93	55.49	75.07	72.99	0.20
97.0	5.40	39.85	43.85	52.19	51.95	49.01	55.77	75.07	72.63	0.19
97.3	5.40	39.94	43.81	51.97	51.60	48.99	55.76	75.07	73.12	0.21
98.0	5.41	40.12	43.30	51.77	51.53	49.23	56.37	74.79	72.51	0.21
98.8	5.41	40.48	42.87	51.40	51.45	49.28	56.69	73.94	71.49	0.21
99.3	5.42	40.62	42.62	51.50	51.43	49.38	56.91	73.90	71.57	0.21
99.5	5.41	40.74	42.63	51.44	51.27	49.42	57.03	73.36	71.15	0.23
100.0	5.42	40.81	42.25	51.12	51.35	49.58	57.31	73.12	70.29	0.22
100.5	5.42	41.05	41.97	51.12	51.29	49.60	57.59	73.10	70.95	0.21
101.3	5.43	41.29	41.72	51.06	50.78	49.68	58.16	71.94	70.18	0.22
101.8	5.43	41.52	41.56	50.81	50.88	49.83	58.36	72.01	70.24	0.21
102.0	5.43	41.58	41.38	50.89	50.72	49.91	58.72	71.99	70.24	0.21
102.8	5.43	41.77	41.03	50.55	50.44	50.07	59.22	72.27	69.68	0.21
103.5	5.44	42.08	40.55	50.35	50.45	50.27	60.13	71.39	69.29	0.23
104.0	5.44	42.37	40.32	50.07	50.23	50.35	60.23	71.41	69.13	0.23
104.3	5.44	42.39	40.23	50.37	50.07	50.47	60.33	70.63	69.29	0.23
104.8	5.45	42.79	40.02	50.00	49.85	50.64	61.17	69.98	69.15	0.23
105.0	5.45	42.75	39.83	49.95	49.99	50.81	61.15	70.53	68.43	0.23