

## Typical Performance Data

CARRIER FREQ. (MHz)	CONVERSION LOSS (dB)	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET (mV)
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
185.0	5.60	39.87	42.64	41.48	41.50	55.49	49.15	79.33	77.29	0.47
186.5	5.60	39.95	42.51	41.31	41.31	55.07	48.98	80.07	77.46	0.47
188.0	5.60	39.88	42.29	41.14	41.17	54.59	48.72	79.11	77.26	0.47
189.0	5.60	39.91	42.13	41.01	41.01	54.45	48.70	79.29	77.02	0.48
189.5	5.59	39.88	41.95	40.97	41.00	54.40	48.68	79.50	77.74	0.48
191.0	5.59	39.76	41.88	40.85	40.88	54.02	48.54	79.84	77.26	0.47
192.5	5.59	39.64	41.32	40.77	40.76	53.58	48.33	79.22	77.41	0.47
193.5	5.59	40.04	41.09	40.67	40.66	53.38	48.28	79.56	77.42	0.49
194.0	5.58	39.57	40.99	40.65	40.66	53.20	48.16	79.68	76.94	0.49
195.5	5.58	39.15	40.43	40.52	40.50	52.75	48.00	80.31	76.48	0.49
197.0	5.58	38.64	39.99	40.41	40.45	52.61	47.96	78.35	77.12	0.50
198.0	5.58	38.43	39.68	40.36	40.35	52.53	47.72	79.79	77.68	0.51
198.5	5.57	38.27	39.38	40.31	40.31	52.41	47.74	80.05	76.06	0.50
200.0	5.58	37.95	39.04	40.17	40.21	51.99	47.60	78.17	76.04	0.51
200.5	5.58	37.80	38.83	40.11	40.10	51.99	47.56	78.51	76.18	0.52
202.0	5.58	37.23	38.09	40.01	39.99	51.96	47.45	79.84	76.57	0.53
203.0	5.57	36.87	37.64	39.91	39.93	51.76	47.38	77.80	75.84	0.54
203.5	5.57	36.64	37.44	39.82	39.79	51.73	47.36	78.95	75.34	0.54
204.5	5.57	36.20	36.98	39.74	39.76	51.53	47.32	78.55	75.42	0.54
205.0	5.57	35.96	36.44	39.69	39.74	51.64	47.20	77.88	75.46	0.55