

Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB	USB	LSB	USB	LSB	USB	LSB	USB	
(MHz)	(dB)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(-dBc)	(mV)
66.0	5.20	38.26	37.56	54.72	55.04	47.30	47.58	74.90	73.48	0.09
66.4	5.20	38.36	37.72	54.40	54.88	47.32	47.66	75.06	73.86	0.09
66.7	5.20	38.50	37.76	54.58	54.66	47.34	47.68	75.52	74.60	0.09
67.1	5.20	38.54	37.92	54.10	54.64	47.34	47.68	74.94	75.12	0.09
67.5	5.20	38.60	38.08	54.36	54.30	47.42	47.72	74.76	75.22	0.09
67.8	5.20	38.72	38.22	53.88	53.98	47.44	47.74	74.84	74.94	0.08
68.2	5.20	38.74	38.40	53.96	53.92	47.48	47.72	75.42	74.58	0.08
68.6	5.20	38.78	38.58	53.56	53.70	47.44	47.74	74.38	74.54	0.08
69.0	5.18	38.88	38.76	53.64	54.10	47.52	47.80	75.04	75.38	0.08
69.3	5.20	38.94	38.94	53.36	54.12	47.56	47.80	74.86	75.12	0.08
69.7	5.20	38.98	39.06	53.16	53.78	47.50	47.76	75.14	74.96	0.08
70.1	5.20	39.12	39.30	53.02	53.70	47.54	47.78	73.92	75.16	0.08
70.4	5.18	39.18	39.46	53.16	53.52	47.58	47.72	73.98	74.88	0.08
70.8	5.20	39.20	39.68	53.10	53.54	47.58	47.72	74.16	75.04	0.08
71.2	5.18	39.24	39.88	53.02	53.34	47.58	47.72	74.02	74.48	0.08
71.5	5.20	39.30	40.00	52.62	53.52	47.60	47.76	73.80	74.98	0.08
71.9	5.18	39.46	40.18	52.78	53.30	47.60	47.80	73.76	74.44	0.08
72.3	5.20	39.50	40.36	52.40	53.58	47.58	47.74	74.30	74.66	0.08
72.6	5.20	39.66	40.50	52.30	53.22	47.64	47.78	73.72	74.46	0.09
73.0	5.18	39.76	40.76	52.16	53.02	47.62	47.78	72.70	73.16	0.09