

Typical Performance Data

CARRIER FREQ. (MHz)	CONVERSION LOSS (dB)	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET (mV)
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
104.0	5.75	44.00	40.36	39.60	39.63	46.08	50.09	71.54	64.27	-0.12
109.4	5.74	43.65	39.80	39.30	39.32	46.33	50.87	72.31	64.71	-0.11
114.8	5.72	46.03	39.54	38.98	38.99	46.63	51.30	73.65	64.68	-0.11
118.4	5.73	46.55	39.15	38.72	38.76	46.75	51.20	74.99	64.74	-0.11
120.2	5.73	46.21	38.88	38.66	38.68	46.88	51.14	75.24	64.26	-0.11
125.6	5.72	43.79	37.74	38.38	38.41	46.71	51.25	76.05	64.77	-0.11
131.0	5.74	41.41	36.65	38.11	38.16	46.80	51.78	76.42	65.40	-0.11
134.6	5.75	39.82	35.86	37.98	38.02	46.93	52.13	77.57	65.53	-0.10
136.4	5.75	39.31	35.61	37.90	37.97	47.01	52.05	76.99	65.63	-0.10
141.8	5.75	38.19	35.02	37.65	37.74	47.45	52.38	77.87	66.22	-0.12
147.2	5.75	36.87	34.30	37.46	37.58	47.53	52.93	77.43	65.79	-0.09
150.8	5.76	36.55	34.12	37.40	37.49	47.54	53.01	77.12	66.03	-0.08
152.6	5.75	36.56	34.13	37.37	37.47	47.87	53.14	76.91	65.90	-0.10
158.0	5.75	36.53	34.07	37.23	37.34	48.53	54.08	76.27	65.56	-0.08
163.4	5.75	36.15	34.03	37.17	37.29	49.21	56.24	75.31	65.88	-0.08
167.0	5.75	36.09	34.06	37.22	37.29	49.33	56.91	74.11	65.51	-0.09
168.8	5.75	36.03	34.16	37.16	37.30	49.47	56.85	73.67	65.43	-0.09
172.4	5.75	36.00	34.31	37.12	37.27	50.03	57.15	73.61	66.29	-0.09
174.2	5.74	36.25	34.46	37.14	37.27	50.26	57.25	73.42	65.85	-0.08
176.0	5.74	36.38	34.68	37.12	37.25	50.39	57.13	72.67	65.63	-0.08