

## Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
(MHz)	(dB)									(mV)
52.0	5.69	42.86	39.69	44.15	44.21	50.41	58.95	77.85	66.29	-0.10
54.7	5.69	41.30	38.12	43.80	43.74	50.66	59.53	76.40	65.83	-0.10
57.4	5.69	39.19	36.53	43.49	43.35	50.60	59.64	75.26	65.54	-0.09
59.2	5.69	37.98	35.67	43.26	43.28	50.57	59.53	74.57	65.23	-0.09
60.1	5.69	37.56	35.29	43.06	43.04	50.56	59.19	74.22	65.09	-0.09
62.8	5.69	36.43	34.51	42.85	42.71	50.32	59.20	73.56	64.62	-0.09
65.5	5.70	35.96	33.92	42.53	42.59	50.00	58.97	72.38	64.13	-0.09
67.3	5.71	35.66	33.67	42.39	42.38	49.89	58.76	72.39	64.00	-0.08
68.2	5.71	35.53	33.66	42.24	42.26	49.73	58.45	72.11	63.79	-0.08
70.9	5.72	35.54	33.66	41.98	42.01	49.49	57.70	71.65	63.68	-0.08
73.6	5.70	35.91	33.98	41.52	41.53	49.28	56.96	71.88	63.48	-0.07
75.4	5.69	36.14	34.00	41.37	41.34	49.27	56.68	71.35	63.24	-0.07
76.3	5.69	36.16	34.06	41.27	41.25	49.32	56.64	71.22	63.20	-0.07
79.0	5.71	35.95	34.02	41.12	41.10	49.29	56.42	70.83	62.88	-0.08
81.7	5.72	36.05	34.11	40.95	40.92	49.23	56.37	70.21	62.83	-0.08
83.5	5.72	36.14	34.25	40.81	40.82	49.00	56.26	70.28	62.68	-0.08
84.4	5.73	36.34	34.38	40.78	40.77	48.99	56.14	69.77	62.76	-0.08
86.2	5.74	36.84	34.71	40.75	40.69	48.73	55.97	69.85	62.71	-0.09
87.1	5.74	36.99	34.87	40.69	40.67	48.44	55.69	69.56	62.69	-0.09
88.0	5.75	37.34	35.01	40.64	40.65	48.44	55.49	69.84	62.83	-0.08