

## Typical Performance Data

CARRIER FREQ.	CONVERSION LOSS	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
(MHz)	(dB)									(mV)
868.0	8.64	40.37	39.42	40.28	40.16	46.63	44.24	59.35	62.87	-1.24
870.1	8.65	40.44	39.60	40.36	40.27	46.71	44.38	59.33	63.25	-1.23
872.3	8.66	40.41	39.49	40.37	40.45	46.95	44.52	59.48	62.84	-1.23
873.0	8.67	40.42	39.34	40.48	40.50	47.02	44.51	59.52	62.94	-1.23
874.4	8.67	40.80	39.30	40.45	40.46	47.21	44.68	59.44	62.90	-1.23
876.5	8.68	40.96	39.03	40.61	40.68	47.35	44.85	59.78	63.10	-1.22
877.9	8.69	40.97	38.86	40.65	40.77	47.56	45.02	59.79	62.97	-1.24
878.7	8.69	41.04	38.97	40.72	40.78	47.62	45.16	59.91	62.83	-1.24
880.8	8.69	41.23	38.95	40.96	41.03	47.85	45.23	60.03	63.19	-1.23
882.2	8.70	41.39	38.79	40.94	40.96	48.04	45.38	59.82	63.02	-1.22
882.9	8.71	41.46	38.73	40.98	41.04	48.15	45.51	60.04	63.04	-1.23
884.3	8.70	41.69	38.80	41.22	41.17	48.41	45.63	60.30	63.38	-1.22
886.5	8.73	41.24	38.56	41.27	41.07	48.52	45.76	59.96	62.74	-1.24
887.9	8.72	41.92	38.57	41.54	41.28	48.70	45.92	60.17	62.61	-1.23
888.6	8.73	41.48	38.50	41.55	41.22	48.75	46.03	60.16	62.54	-1.23
890.7	8.75	41.30	38.38	41.60	41.30	48.99	46.19	60.01	62.41	-1.24
892.9	8.75	41.13	38.40	41.87	41.39	49.19	46.47	59.93	62.57	-1.26
893.6	8.76	40.96	38.38	42.02	41.37	49.20	46.48	59.96	62.14	-1.26
894.3	8.77	40.78	38.18	42.08	41.39	49.24	46.54	59.88	61.92	-1.27
895.0	8.75	40.87	38.27	42.42	41.73	49.31	46.61	60.07	62.33	-1.26