

DC Passing Fixed Attenuator

NAT-EDU1959

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
100	2.98	37.84
120	3.02	39.31
140	3.05	39.24
150	3.06	38.74
170	3.08	37.24
190	3.09	35.82
200	3.10	35.21
220	3.10	34.08
240	3.10	33.10
250	3.10	32.65
270	3.10	31.89
290	3.11	31.23
300	3.11	30.92
320	3.11	30.41
340	3.12	29.97
350	3.12	29.84
370	3.12	29.56
390	3.13	29.17
400	3.13	28.99
420	3.13	28.62
440	3.14	28.29
450	3.15	28.11
470	3.17	27.87
500	3.21	27.64