

DC Passing Fixed Attenuator

NAT-EDU1960

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
100	6.10	41.09
120	6.11	42.76
140	6.11	40.85
150	6.11	39.84
170	6.12	38.13
190	6.12	36.80
200	6.12	36.25
220	6.12	35.18
240	6.13	34.29
250	6.13	33.91
270	6.14	33.23
290	6.14	32.71
300	6.15	32.45
320	6.16	31.98
340	6.17	31.49
350	6.17	31.29
370	6.18	30.97
390	6.19	30.55
400	6.19	30.34
420	6.21	29.95
440	6.22	29.58
450	6.23	29.40
470	6.26	29.05
500	6.31	28.49