

DC Passing Fixed Attenuator

NAT-EDU1961

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
100	9.96	33.40
120	10.01	33.34
140	10.05	33.31
150	10.07	33.32
170	10.09	33.40
190	10.11	33.56
200	10.11	33.67
220	10.11	33.95
240	10.11	34.24
250	10.12	34.34
270	10.12	34.49
290	10.12	34.55
300	10.12	34.55
320	10.13	34.58
340	10.13	34.75
350	10.14	34.83
370	10.14	34.81
390	10.14	34.80
400	10.15	34.81
420	10.16	34.75
440	10.17	34.67
450	10.18	34.64
470	10.20	34.68
500	10.24	34.89