

# Type-N/BNC Adaptenuator

# NF-BF-3

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-FEMALE RETURN LOSS (dB)	N-FEMALE RETURN LOSS (dB)
1	3.00	46.06	46.06
5	2.98	46.06	46.06
10	3.00	46.06	46.06
50	2.99	46.06	46.06
100	3.04	40.09	46.06
500	3.07	29.42	30.71
1000	3.13	28.30	25.66
1500	3.14	30.71	25.66
1700	3.21	32.26	26.44
2000	3.21	34.15	30.71

REV. X1  
NF-BF-3  
061113  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

