

Type-N/BNC Adaptenuator

NF-BM-3

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-MALE RETURN LOSS (dB)	N-FEMALE RETURN LOSS (dB)
1	2.99	46.06	46.06
5	2.98	46.06	46.06
10	3.00	46.06	46.06
50	3.00	46.06	46.06
100	3.02	46.06	40.09
500	3.05	30.71	30.71
1000	3.12	25.66	27.32
1500	3.14	25.66	29.42
1700	3.19	27.32	29.42
2000	3.24	32.26	29.42

REV. X1
NF-BM-3
061113
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

