

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
10.0	0.03	46.7	46.9
50.0	0.06	38.6	38.3
100.0	0.08	39.5	39.0
200.0	0.11	39.3	39.5
300.0	0.14	54.0	43.4
400.0	0.17	33.4	33.4
500.0	0.19	37.4	37.2
600.0	0.20	33.9	33.7
700.0	0.22	32.1	32.1
800.0	0.24	38.6	37.9
900.0	0.26	29.3	29.3
1000.0	0.27	42.4	44.1
1100.0	0.29	28.8	28.7
1250.0	0.31	27.9	27.9
1500.0	0.34	32.3	33.4
1750.0	0.37	30.0	30.2
2000.0	0.40	28.0	28.4
2250.0	0.42	36.0	36.9
2500.0	0.45	27.9	27.9
2750.0	0.47	44.6	40.3
3000.0	0.49	29.4	28.9
3250.0	0.51	36.4	39.4
3500.0	0.54	31.6	29.6
3750.0	0.56	32.4	35.5
4000.0	0.58	33.3	30.3
4500.0	0.62	34.5	29.6
5000.0	0.66	39.6	30.9
5500.0	0.69	42.2	31.5
6000.0	0.73	41.1	41.7
6500.0	0.77	32.5	35.8
7000.0	0.79	31.3	33.0
7500.0	0.85	27.2	26.6
8000.0	0.89	23.2	21.9
8500.0	0.94	21.3	20.2
9000.0	0.97	21.6	20.5
9500.0	0.99	24.2	22.0
10000.0	1.02	22.8	22.1
10500.0	1.05	22.5	24.7
11000.0	1.07	22.3	26.6
11500.0	1.12	20.7	22.9
12000.0	1.18	18.7	20.8
12500.0	1.22	18.4	19.6
13000.0	1.24	18.8	19.2
13500.0	1.24	18.7	18.9
14000.0	1.24	21.0	20.6
14500.0	1.28	24.0	23.8
15000.0	1.30	25.1	26.6
15500.0	1.30	25.3	27.6
16000.0	1.33	27.5	26.3
16500.0	1.36	25.1	25.9
17000.0	1.39	24.3	26.1
17500.0	1.43	21.2	22.4
18000.0	1.42	19.9	21.1