

Band Pass Filter

RBP-EDU1130/1

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	87.48	0.04	130.0	19.77
50.0	46.18	0.02	132.0	19.02
60.0	44.52	0.04	132.2	18.94
100.0	28.90	0.52	133.0	18.72
108.0	16.74	1.36	134.0	18.45
114.0	8.36	4.16	135.0	18.23
118.0	4.63	10.10	136.0	18.06
132.2	2.21	23.56	137.0	17.92
135.0	2.18	19.23	138.0	17.83
140.0	2.20	16.71	139.0	17.77
144.0	2.25	17.73	140.0	17.78
147.2	2.35	19.46	142.0	17.90
160.0	4.51	11.45	143.0	18.02
165.0	8.94	4.32	144.0	18.18
170.0	15.89	1.79	145.0	18.38
180.0	31.02	0.71	146.0	18.61
220.0	45.50	0.20	147.0	18.87
300.0	57.19	0.08	147.2	18.94
400.0	71.85	0.05	148.0	19.16
500.0	86.95	0.05	150.0	19.89