

Surface Mount High Pass Filter

RHP-EDU2189

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	97.06	0.05	800	1.61
50	98.59	0.05	850	1.26
100	99.77	0.05	900	1.03
250	62.67	0.08	950	0.88
350	47.49	0.16	980	0.81
580	32.16	0.61	1000	0.76
584	30.11	0.63	1020	0.73
610	20.02	0.80	1050	0.67
680	3.53	4.79	1100	0.60
685	2.96	5.64	1130	0.57
700	1.78	8.74	1150	0.54
800	0.56	36.39	1200	0.50
1000	0.42	18.93	1250	0.46
1100	0.40	18.53	1300	0.42
1300	0.35	19.62	1350	0.39
1500	0.31	20.67	1400	0.37
1600	0.29	21.24	1450	0.35
1800	0.27	22.54	1500	0.33
2000	0.27	23.65	1550	0.31
2200	0.26	24.05	1600	0.29
2400	0.28	22.66	1650	0.28
2600	0.30	20.13	1700	0.27
2800	0.34	17.31	1750	0.26
3000	0.42	14.82	1800	0.25