

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.00	0.27	25.21
19.00	0.27	27.89
28.00	0.26	29.13
37.00	0.26	29.62
46.00	0.26	29.62
55.00	0.26	29.32
64.00	0.27	28.81
73.00	0.27	28.16
82.00	0.27	27.41
91.00	0.28	26.59
100.00	0.28	25.72
105.00	0.28	25.24
110.00	0.28	24.75
115.00	0.29	24.25
120.00	0.29	23.75
125.00	0.30	23.27
128.00	0.30	22.97
131.00	0.30	22.67
134.00	0.30	22.37
137.00	0.30	22.09
140.00	0.30	21.80
144.00	0.31	21.41
148.00	0.31	21.04
152.00	0.31	20.67
156.00	0.31	20.32
160.00	0.31	19.94
164.00	0.32	19.59
168.00	0.32	19.23
172.00	0.32	18.89
176.00	0.32	18.54
180.00	0.32	18.21
187.00	0.32	17.62
194.00	0.33	17.07
201.00	0.34	16.51
208.00	0.34	15.98
215.00	0.35	15.47
222.00	0.36	14.96
229.00	0.37	14.47
236.00	0.38	14.00
243.00	0.40	13.53
250.00	0.42	13.08