

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.15	1.74	9.52
0.18	1.56	10.62
0.21	1.43	11.52
0.24	1.34	12.27
0.27	1.27	12.91
0.30	1.22	13.45
0.40	1.09	14.89
0.60	0.94	16.76
0.80	0.86	18.03
1.00	0.80	18.97
2.00	0.68	21.53
10.00	0.66	22.97
20.00	0.70	21.64
30.00	0.74	20.26
40.00	0.77	18.92
50.00	0.81	17.65
60.00	0.84	16.50
70.00	0.88	15.43
80.00	0.92	14.48
90.00	0.96	13.61
95.00	0.98	13.21
100.00	1.01	12.81
105.00	1.03	12.45
110.00	1.05	12.09
115.00	1.08	11.75
120.00	1.11	11.43
125.00	1.14	11.12
130.00	1.17	10.81
135.00	1.20	10.53
140.00	1.24	10.25
145.00	1.27	9.98
150.00	1.31	9.72
155.00	1.35	9.48
160.00	1.38	9.24
165.00	1.42	9.01
170.00	1.46	8.79
176.00	1.50	8.53
182.00	1.54	8.28
188.00	1.58	8.05
194.00	1.61	7.82
200.00	1.65	7.60