

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
2.00	2.54	5.37
2.20	2.28	5.95
2.40	2.06	6.50
2.60	1.87	7.03
2.80	1.71	7.56
3.00	1.57	8.08
3.60	1.24	9.47
4.20	1.01	10.77
4.80	0.84	11.96
5.40	0.72	13.12
6.00	0.62	14.20
10.00	0.36	21.05
15.00	0.30	34.60
20.00	0.31	30.03
25.00	0.36	23.08
30.00	0.42	19.61
34.00	0.48	17.70
38.00	0.55	16.23
42.00	0.62	15.01
46.00	0.70	13.96
50.00	0.80	13.04
52.00	0.84	12.62
54.00	0.89	12.23
56.00	0.94	11.86
58.00	0.99	11.50
60.00	1.04	11.16
63.00	1.12	10.69
66.00	1.21	10.29
69.00	1.29	9.86
72.00	1.39	9.44
75.00	1.48	9.06
76.00	1.51	8.93
77.00	1.54	8.83
78.00	1.58	8.71
79.00	1.61	8.58
80.00	1.64	8.46
83.00	1.74	8.15
86.00	1.84	7.82
89.00	1.95	7.53
92.00	2.05	7.25
95.00	2.16	6.98