

RF Transformer

TRS1-1T-13-2A+

Typical Performance Data

FREQUENCY MHz	INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	OUTPUT RETURN LOSS (dB)
50.0	0.18	40.67	40.14
60.0	0.19	40.10	39.35
70.0	0.19	39.74	38.47
80.0	0.20	39.29	37.75
90.0	0.20	38.82	37.07
100.0	0.20	38.31	36.50
150.0	0.22	36.37	34.16
200.0	0.22	34.96	32.40
250.0	0.24	34.03	31.22
300.0	0.25	32.97	30.03
350.0	0.26	32.10	29.14
400.0	0.27	31.47	28.42
450.0	0.28	30.60	27.61
500.0	0.29	30.18	27.15
550.0	0.30	29.37	26.53
600.0	0.31	28.78	26.10
650.0	0.32	28.11	25.64
700.0	0.34	27.44	25.18
750.0	0.35	26.79	24.77
800.0	0.36	25.99	24.28
850.0	0.38	25.36	23.95
900.0	0.39	24.56	23.30
950.0	0.41	23.93	22.95
1000.0	0.42	23.18	22.33