

Non-Catalog Model

Frequency Mixer

Level 7 (LO Power +7 dBm)

ADE-32

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CD542

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	2500		3200	MHz
	RF (fL to fU)	2500		3200	MHz
	IF	0		1200	MHz
Conversion Loss			5.4	9.4	dB
LO-RF Isolation		20	29		dB
LO-IF Isolation		20	30		dB
IP3 Input			+15		dBm
1 dB Comp. Input Power			+1		dBm

Note: Aqueous washable.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	6
RF	4
IF	3
GROUND	1, 2, 5

Electrical Schematics

