

Non-Catalog Model

Frequency Mixer

MBA-10VL

Level 0 (LO Power +0 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : SM2

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	800		1000	MHz
	RF (fL to fU)	800		1000	MHz
	IF	0		200	MHz
Conversion Loss			7.4	9.8	dB
LO-RF Isolation		14	18		dB
LO-IF Isolation		8	14		dB
1 dB Comp. Input Power			-3		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	10
RF	5
IF	3
GROUND	1, 2, 4, 6, 7, 8, 9

Electrical Schematics

