

Non-Catalog Model

Frequency Mixer

SBL-1-1LH

Level 10 (LO Power +10 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	0.2		400	MHz
	RF (fL to fU)	0.2		400	MHz
	IF	0		400	MHz
Conversion Loss	mid band		5.2	7.0	dB
	Total Range			9.0	dB
LO-RF Isolation	Low Range	45	67		dB
	Mid Range	30	64		dB
	Upper Range	25	51		dB
LO-IF Isolation	Low Range	30	62		dB
	Mid Range	25	52		dB
	Upper Range	20	34		dB
1 dB Comp. Input Power			+5		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally

Electrical Schematics

