## **Frequency Mixer**

**SYM-860** 

Level 7 (LO Power +7 dBm)

## **Important Note**

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

<b>CASE</b>	STYL	.E : 1	ΓTΤ	166
-------------	------	--------	-----	-----

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C						
Parameter		Min.	Тур.	Max.	Units	
Frequency	LO (fL to fU)	800		1050	MHz	
	RF (fL to fU)	800		1050	MHz	
	IF	0		250	MHz	
<b>Conversion Loss</b>			5.6	7.0	dB	
LO-RF Isolation		25	39		dB	
LO-IF Isolation		20	37		dB	
1 dB Comp. Input Power			+1		dBm	

Note: Units are non-hermetic.

MAXIMUM RATINGS				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power	50mW			
IF Current	40mA			

PIN CONNECTIONS			
LO	2		
RF	1		
IF	3		
GROUND	4, 5, 6		

## **Electrical Schematics**

