

Non-Catalog Model

Frequency Mixer Level 7 (LO Power +7 dBm)

TSM-1

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : A11

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1		600	MHz
	RF (fL to fU)	1		600	MHz
	IF	0		600	MHz
Conversion Loss	mid band		5.7	7.5	dB
	Total Range			8.5	dB
LO-RF Isolation	Low Range	45	60		dB
	Mid Range	35	45		dB
	Upper Range	25	35		dB
LO-IF Isolation	Low Range	45	55		dB
	Mid Range	30	40		dB
	Upper Range	25	35		dB
1 dB Comp. Input Power			+1		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Hermetically sealed

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally

Electrical Schematics

