

Non-Catalog Model

Frequency Mixer

Level 7 (LO Power +7 dBm)

TUF-11ASM

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : NNN150

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1400		1900	MHz
	RF (fL to fU)	1400		1900	MHz
	IF	40		500	MHz
Conversion Loss			6.8	8.6	dB
LO-RF Isolation		20	33		dB
LO-IF Isolation		15	29		dB
1 dB Comp. Input Power			+1		dBm

Note: Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

Electrical Schematics

