

Non-Catalog Model

Frequency Mixer

TUF-860LH

Level 10 (LO Power +10 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : B02

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	800		1050	MHz
	RF (fL to fU)	800		1050	MHz
	IF	0		250	MHz
Conversion Loss			6.3	7.9	dB
LO-RF Isolation		25	35		dB
LO-IF Isolation		18	27		dB
1 dB Comp. Input Power			+5		dBm

Note: Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

Electrical Schematics

