



Outline Dimensions

AW257-2



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE #	A	B	C	D	E	F	G	H	J	K	L
AW257-2	8.06 (204.72)	3.25 (82.55)	2.38 (60.45)	.125 (3.18)	7.560 (192.02)	2.625 (66.68)	.144 (3.66)	.890 (22.61)	.44 (11.18)	7.06 (179.32)	.88 (22.35)

CASE #	M	N	WT, GRAMS	WT WITHOUT HEATSINK, GRAMS
AW257-2	3.13 (79.50)	.75 (19.05)	1240	850

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Mounting hole locations $\nabla .005$

Notes:

- Case material: Aluminum alloy.
- Case Finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS