


Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K
BV278	6.00 (152.40)	4.50 (114.30)	1.38 (35.05)	.15 (3.81)	5.700 (144.78)	.15 (3.81)	4.200 (106.68)	.38 (9.65)	2.25 (57.15)	.75 (19.05)

CASE #	L	M	WT. GRAMS
BV278	.75 (19.05)	.156 (3.96)	960

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black Anodize.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified