


Outline Dimensions



* OVERALL CONNECTOR DIMENSION [CONNECTOR SHAPE MAY VARY]

BZ2421H SERIES
 SMPR FEMALE (CONN-1)
 SMPR FEMALE (CONN-2)

| CASE STYLE # | A | | B | C1 | C2 | D | E1 | E2 | F | | G | H | T | | WEIGHT GRAMS |
|--------------|-------|--------|---------------|----------------|----------------|---------------|----------------|----------------|------------------------|------------------------|----|----|------|------|--------------|
| | INCH | MM | | | | | | | 047U-ASMPR+ | 047-ASMPR+ | | | INCH | MM | |
| BZ2421H3 | 3.00 | 76.20 | .14 (3.50) | .135 (3.43) | .287 (7.35) | .14 (3.50) | .135 (3.43) | .289 (7.35) | .048 MAX (1.22 MAX) | .069 MAX (1.75 MAX) | -- | -- | .05 | 1.27 | 1.4 |
| BZ2421H6 | 6.00 | 152.40 | | | | | | | | | -- | -- | .05 | 1.27 | 2.2 |
| BZ2421H12 | 12.00 | 304.80 | | | | | | | | | -- | -- | .10 | 2.54 | 4.0 |
| | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 047 Hand-Flex™ Coaxial Cable.
2. "A" represents length of cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified