




Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$



| CASE # | A | B | C | D | E | F | G | H | J | K |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| CA1389 | .045 (1.15) | .053 (1.35) | .073 (1.85) | .089 (2.25) | .031 (0.80) | .039 (1.00) | .079 (2.00) | .091 (2.30) | .051 (1.30) | .051 (1.30) |

| CASE # | L | M | N | P | Q | R | S | T | WT. GRAM |
|--------|----------------|---|----------------|----------------|----------------|-----------------|----------------|---|----------|
| CA1389 | .026 (0.65) | - | .006 (0.15) | .012 (0.30) | .004 (0.09) | .007 (0.165) | .012 (0.31) | - | .010 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Matte Tin plate.
- Primary dimensions are in millimeters.