

CR540^(inch)_{mm}

A	B	C	D	E	F	G	H	J	
.517 13.132	.800 20.320		.100 2.540	.385 9.779	.100 2.540	.100 2.540	.047 1.194	.065 1.651	
K	L	M	N	P	Q	R	S	T	wt. grams.
.065 1.651	.540 13.716	.665 16.891	.300 7.620						4.000

Tolerance: .x ± .1 .xx ± .03 .xxx ± .015 inch.

Notes:

- Material and Finish:
 - Base: Glass epoxy laminate.
 - Cover: Copper-Nickel alloy.
 - Lead Finish: For RoHS Models: - Tin Plate Over Nickel.
For Non-RoHS Models: - Tin/Lead Plate or Tin Plate Over Nickel.



