



Outline Dimensions

DDD131



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
DDD131	7.00 (177.80)	3.25 (82.55)	3.13 (79.50)	.25 (6.35)	6.500 (165.10)	.38 (9.65)	2.500 (63.50)	.156 (3.96)	.88 (22.35)	.43 (10.92)	.62 (15.75)	1.00 (25.40)	2.63 (66.68)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
DDD131	.125 (3.18)	.50 (12.70)	6.00 (152.40)	2.23 (56.64)	8.35 (212.09)	1780	510

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heatsink finish: Black anodize if supplied with heatsink.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified