



## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
DG1847	.157 (4.00)	.157 (4.00)	.039 (1.00)	.008 (0.20)	.104 (2.65)	.104 (2.65)	.009 (0.23)	-- --	.016 (0.40)	.020 (0.50)

CASE #	L	M	N	P	Q	R	WT. GRAM
DG1847	.166 (4.22)	.166 (4.22)	.102 (2.59)	.012 (0.31)	.020 (0.51)	.102 (2.59)	.04

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See model Data sheet.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.