


### Outline Dimensions



| CASE#  | A             | B              | D               | E              | WT. GRAM |
|--------|---------------|----------------|-----------------|----------------|----------|
| DJ1208 | .25<br>(6.35) | .80<br>(20.32) | 1.79<br>(45.47) | .72<br>(18.29) | 49       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

#### Notes:

1. Case material: Brass
2. Finish: Nickel plate.