



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1458	.44 (11.18)	.750 (19.05)	.295 (3.56)	.200 (5.08)	.07 (1.78)	.100 (2.54)	.125 (3.18)	.697 (17.70)	.200 (5.08)	.470 (11.94)	.150 (3.81)	.100 (2.54)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.