


## Outline Dimensions

NL1008C-2



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAM
NL1008C-2	.098 (2.50)	.079 (2.00)	.043 (1.10)	.022 (.55)	.016 (.40)	.012 (.30)	.028 (.70)	.016 (.40)	.039 (1.00)	.140 (3.55)	.043 (1.10)	.159 (4.05)	.019

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Open style, ceramic base.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Line width should be designed to match  $50\Omega$  characteristic depending on PCB material and thickness.