

PPP83^{inch}_{mm}

A	B	C	D	E	F	G	H	J	
.75 19.050	.38 9.652	.20 5.080	.010 0.254	.05 1.270	.020 0.508	.200 5.080	.075 1.905	.200 5.080	
K	L	M	N	P	Q	R	S	T	wt. grams.
.14 3.556	.060 1.524								1.600

Tolerance: .x ± .1 .xx ± .03 .xxx ± .015 inch.

Notes:

- Material and Finish:
 - Case material: plastic.
 - Lead Finish: For RoHS Models: - Tin Plate over Nickel or Tin-Silver-Nickel plate
For Non-RoHS Models: - Tin-Lead Plate or Tin Plate or Tin-Silver-Nickel plate.
- Special Tolerances:
 - Lead width ±.010 inch; lead thickness ±.003 inch.



