


Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIM
[CONNECTOR SHAPE MAY VARY]

RF2512 SERIES

2.92mm MALE (CONN-1)

2.92mm MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS
	FEET	METERS						INCH	MM	
RF2512-2	2.00	.61	.36 (9.25)	.312 (7.93)	.36 (9.25)	.312 (7.93)	.100 (2.54)	+.50/-0	+12.7/-0	30
RF2512-3	3.00	.91						+ .72/-0	+18.3/-0	35
RF2512-3.28	3.28	1.00						+ .79/-0	+20.0/-0	36
RF2512-6	6.00	1.83						+1.44/-0	+36.6/-0	50

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

1. High Performance very Flexible Cable.