


Outline Dimensions



SE2633 SERIES N MALE (CONN)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F FL086-ANM+	T		WEIGHT GRAMS
	INCH	MM								INCH	MM	
SE2633-6	6.00	152.40	.88 (22.0)	.750 (19.0)	.375 (9.5)	.88 (22.0)	.750 (19.0)	.375 (9.5)	.106±.004 (2.64±0.1)	0.05	1.27	71.91
SE2633-12	12.00	304.80								0.10	2.54	74.82
SE2633-24	24.00	609.60								0.15	3.81	80.64

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 086 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.