


Outline Dimensions



* OVERALL CONNECTOR DIMENSION
(CONNECTOR SHAPE MAY VARY)

SG2636 SERIES N MALE (CONN)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F FL141-ANM+	T		WEIGHT GRAMS
	INCH	MM								INCH	MM	
SG2636-6	6	152.4	.88 (22.0)	.750 (19.0)	.375 (9.5)	.88 (22.0)	.750 (19.0)	.375 (9.5)	.163±.006 (4.14±0.15)	0.05	1.27	75.64
SG2636-12	12	304.8								0.10	2.54	82.28
SG2636-24	24	609.6								0.15	3.81	95.57

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 141 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS