


Case Style

Outline Dimensions

UL

UL3032



UL3032 SERIES SSMP FEMALE (CONN)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WT. (GRAMS)
	INCH	MM							FL47U-ASSMP+ (UN-JACKETED)	FL47-ASSMP+ (JACKETED)	INCH	MM	
UL3032-6	6.00	157.40									.05	1.27	1.44
UL3032-12	12.00	304.80	.14	.093	.303	.14	.093	.303	.046±.004	.055±.004	.10	2.54	2.28
			[3.56]	[2.36]	[7.70]	[3.56]	[2.36]	[7.70]	[1.17±0.1]	[1.40±0.1]			

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2 Pl.±.03; 3 Pl. ±.015

Note:

1. 047 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



RF/IF MICROWAVE COMPONENTS