




CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
UU2303	1.98 (50.29)	1.46 (37.08)	.40 (10.16)	.17 (4.32)	1.640 (41.66)	.73 (18.54)	.137 (3.48)	.99 (25.15)	.20 (5.08)	.500 (12.70)	.24 (6.10)	62

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS