

Typical Performance Data

FREQ.	INSERTION LOSS	Right Angle MCX VSWR	Right Angle MCX VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	-0.09	1.02	1.02
0.10	-0.19	1.02	1.02
0.20	-0.26	1.03	1.03
0.40	-0.35	1.04	1.02
0.60	-0.42	1.03	1.02
0.80	-0.48	1.03	1.04
1.00	-0.53	1.05	1.06
1.20	-0.57	1.06	1.07
1.40	-0.61	1.06	1.05
1.60	-0.65	1.05	1.04
1.80	-0.69	1.07	1.08
2.00	-0.73	1.10	1.12
2.20	-0.76	1.10	1.11
2.40	-0.79	1.07	1.08
2.60	-0.81	1.04	1.04
2.80	-0.84	1.06	1.07
3.00	-0.87	1.10	1.11
3.20	-0.91	1.12	1.13
3.40	-0.93	1.11	1.12
3.60	-0.95	1.08	1.09
3.80	-0.97	1.05	1.06
4.00	-0.99	1.06	1.06
4.20	-1.02	1.08	1.09
4.40	-1.05	1.10	1.11
4.60	-1.08	1.12	1.14
4.80	-1.10	1.14	1.15
5.00	-1.12	1.11	1.12
5.20	-1.13	1.07	1.08
5.40	-1.15	1.06	1.08
5.60	-1.19	1.12	1.14
5.80	-1.23	1.19	1.20
6.00	-1.26	1.24	1.25