

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.04	46.4	46.8
500.0	0.04	46.4	46.8
1000.0	0.11	55.8	47.0
1100.0	0.11	55.8	47.0
1200.0	0.11	55.8	47.0
1300.0	0.11	55.8	47.0
1400.0	0.16	42.3	40.7
1500.0	0.16	42.3	40.7
1600.0	0.16	42.3	40.7
1700.0	0.16	42.3	40.7
1800.0	0.16	42.3	40.7
1900.0	0.16	42.3	40.7
2000.0	0.20	37.7	37.8
2400.0	0.20	37.7	37.8
3000.0	0.20	37.7	37.8
4000.0	0.26	35.6	36.0
5000.0	0.31	36.8	38.6
5500.0	0.31	36.8	38.6
6000.0	0.36	34.7	34.3
6500.0	0.36	34.7	34.2
7000.0	0.36	34.7	34.2
7500.0	0.36	34.7	34.2
8000.0	0.36	34.7	34.2
8500.0	0.41	28.0	26.2
9000.0	0.41	28.0	26.2
9500.0	0.41	28.0	26.2
10000.0	0.41	28.0	26.2
10500.0	0.49	25.4	24.2
11000.0	0.49	25.4	24.2
11500.0	0.49	25.4	24.2
12000.0	0.52	23.1	26.1
12500.0	0.52	23.1	26.2
13000.0	0.54	29.3	35.5
13500.0	0.54	29.3	35.5
14000.0	0.61	22.5	23.7
14500.0	0.61	22.5	23.7
15000.0	0.52	24.5	29.5
15500.0	0.65	24.2	24.9
16000.0	0.65	24.2	24.9
16500.0	0.75	23.3	25.0
17000.0	0.75	23.3	25.0
17500.0	0.68	25.8	28.4
18000.0	0.70	23.7	23.8